



Features:

- 2 x front speakers
- 1 x Centre speakers
- 2 x Rear speakers
- 1 x sub
- Aluminium finish

A first class start

On the market for your first multi-channel surround system, but a bit squeezed on the financial side? Look no further: Choose Spectrum 5.1 or the new HomeCinema1 for a solution you'll love, at a price you can afford. Both compact multi-channel speaker systems get you off to a first class start within our world.

Front left, front right, rear left, rear right and centre! Whilst this may sound like something a boot camp drill sergeant would shout at you, we're fortunately only describing the different channels of sound reproduction delivered by the Spectrum 5.1 system.

HomeCinema1 centre and satellite speakers may be placed freely within your listening sphere, thanks to the enclosed 30 metres of speaker cable. The HomeCinema1 active subwoofer rounds out the system, delivering accurate bass effects from its down-firing 165 mm membrane.

We recommend placement of Spectrum and HomeCinema1 satellite speakers on optional Galant floor stands or wall mounting them via the enclosed brackets. All speakers are available in your choice of black or silver.





	Centre	Satellite
System	Closed Box	Closed Box
Recommended power amplifier	AV-amps. Up to 100W RMS pr. channel	AV-amps. Up to 100W RMS pr. channel
Frequency range +/- 4 dB	85-20,000Hz	85-20,000Hz
Sensitivity (2,83V / 1M)	87dB	87dB
Impedance	4-8 Ohm	4-8 Ohm
Driver	2 x 70mm Full Range Shielded	70mm Full Range
Speaker input terminals	Clip	Clip
Dimensions (HxWxD)	90x195x105mm	125x90x105mm
Weight	1.2Kg	0.7Kg
Wall Brackets		Built in
Accessories		Rubber feet, 3 x 3m speaker cable, 2 x 5m speaker cable, 1 x 2m RCA cable

	Subwoofer
System	Bass reflex
Sinus Max power	35W
Music Max power	60W
Recommended power amplifier AV-amps.	Up to 100W RMS pr. channel
Frequency range +/- 4 dB	45 - 250Hz
Subwoofer	165mm downfiring
Crossover Frequency	0 - 180°
Volume control	Yes
Subwoofer RCA line-in	Yes
Speaker input terminals	Left / Right Clip
Speaker outputs	Left / Right Clip
Mains voltage	230/240V - 50/60Hz
Power consumption	55W
Dimensions (HxWxD)	300x225x300mm
Weight	5.5Kg

Contact our sales department for further information.

Eltax Denmark +45 9641 1500
 Eltax UK +44(0) 1327860789
 Eltax Germany +49(0) 461 28080
 Eltax France +33(0) 466 680626
 Eltax Benelux +32(0) 2 354 5363

eltax ▶
 just play